


BODENEINBAULEUCHTEN

Jedi Einbauleuchten -
L. 616mm

Art.-Nr.
1E2669

LICHTFARBE	LICHTVERTEILUNG	OUTPUT
3000K 80	Grazing 15° / 76°	28W 2961lm
BETRIEBSGERÄT STEUERUNG	FARBE	
220-240Vac ON-OFF		



Alle Daten auf der Maßzeichnung sind in mm angegeben.



3.8

IP66

IP67

IP68

IP69

IK10





The diagram shows a light beam with a beam spread of 120°. The beam diameter at 1600 units is 800 units. The beam diameter at 1601 units is 1601 units. The beam diameter at 1602 units is 1602 units. The beam diameter at 1603 units is 1603 units. The beam diameter at 1604 units is 1604 units. The beam diameter at 1605 units is 1605 units. The beam diameter at 1606 units is 1606 units. The beam diameter at 1607 units is 1607 units. The beam diameter at 1608 units is 1608 units. The beam diameter at 1609 units is 1609 units. The beam diameter at 1610 units is 1610 units. The beam diameter at 1611 units is 1611 units. The beam diameter at 1612 units is 1612 units. The beam diameter at 1613 units is 1613 units. The beam diameter at 1614 units is 1614 units. The beam diameter at 1615 units is 1615 units. The beam diameter at 1616 units is 1616 units. The beam diameter at 1617 units is 1617 units. The beam diameter at 1618 units is 1618 units. The beam diameter at 1619 units is 1619 units. The beam diameter at 1620 units is 1620 units. The beam diameter at 1621 units is 1621 units. The beam diameter at 1622 units is 1622 units. The beam diameter at 1623 units is 1623 units. The beam diameter at 1624 units is 1624 units. The beam diameter at 1625 units is 1625 units. The beam diameter at 1626 units is 1626 units. The beam diameter at 1627 units is 1627 units. The beam diameter at 1628 units is 1628 units. The beam diameter at 1629 units is 1629 units. The beam diameter at 1630 units is 1630 units. The beam diameter at 1631 units is 1631 units. The beam diameter at 1632 units is 1632 units. The beam diameter at 1633 units is 1633 units. The beam diameter at 1634 units is 1634 units. The beam diameter at 1635 units is 1635 units. The beam diameter at 1636 units is 1636 units. The beam diameter at 1637 units is 1637 units. The beam diameter at 1638 units is 1638 units. The beam diameter at 1639 units is 1639 units. The beam diameter at 1640 units is 1640 units. The beam diameter at 1641 units is 1641 units. The beam diameter at 1642 units is 1642 units. The beam diameter at 1643 units is 1643 units. The beam diameter at 1644 units is 1644 units. The beam diameter at 1645 units is 1645 units. The beam diameter at 1646 units is 1646 units. The beam diameter at 1647 units is 1647 units. The beam diameter at 1648 units is 1648 units. The beam diameter at 1649 units is 1649 units. The beam diameter at 1650 units is 1650 units. The beam diameter at 1651 units is 1651 units. The beam diameter at 1652 units is 1652 units. The beam diameter at 1653 units is 1653 units. The beam diameter at 1654 units is 1654 units. The beam diameter at 1655 units is 1655 units. The beam diameter at 1656 units is 1656 units. The beam diameter at 1657 units is 1657 units. The beam diameter at 1658 units is 1658 units. The beam diameter at 1659 units is 1659 units. The beam diameter at 1660 units is 1660 units. The beam diameter at 1661 units is 1661 units. The beam diameter at 1662 units is 1662 units. The beam diameter at 1663 units is 1663 units. The beam diameter at 1664 units is 1664 units. The beam diameter at 1665 units is 1665 units. The beam diameter at 1666 units is 1666 units. The beam diameter at 1667 units is 1667 units. The beam diameter at 1668 units is 1668 units. The beam diameter at 1669 units is 1669 units. The beam diameter at 1670 units is 1670 units. The beam diameter at 1671 units is 1671 units. The beam diameter at 1672 units is 1672 units. The beam diameter at 1673 units is 1673 units. The beam diameter at 1674 units is 1674 units. The beam diameter at 1675 units is 1675 units. The beam diameter at 1676 units is 1676 units. The beam diameter at 1677 units is 1677 units. The beam diameter at 1678 units is 1678 units. The beam diameter at 1679 units is 1679 units. The beam diameter at 1680 units is 1680 units. The beam diameter at 1681 units is 1681 units. The beam diameter at 1682 units is 1682 units. The beam diameter at 1683 units is 1683 units. The beam diameter at 1684 units is 1684 units. The beam diameter at 1685 units is 1685 units. The beam diameter at 1686 units is 1686 units. The beam diameter at 1687 units is 1687 units. The beam diameter at 1688 units is 1688 units. The beam diameter at 1689 units is 1689 units. The beam diameter at 1690 units is 1690 units. The beam diameter at 1691 units is 1691 units. The beam diameter at 1692 units is 1692 units. The beam diameter at 1693 units is 1693 units. The beam diameter at 1694 units is 1694 units. The beam diameter at 1695 units is 1695 units. The beam diameter at 1696 units is 1696 units. The beam diameter at 1697 units is 1697 units. The beam diameter at 1698 units is 1698 units. The beam diameter at 1699 units is 1699 units. The beam diameter at 1700 units is 1700 units. The beam diameter at 1701 units is 1701 units. The beam diameter at 1702 units is 1702 units. The beam diameter at 1703 units is 1703 units. The beam diameter at 1704 units is 1704 units. The beam diameter at 1705 units is 1705 units. The beam diameter at 1706 units is 1706 units. The beam diameter at 1707 units is 1707 units. The beam diameter at 1708 units is 1708 units. The beam diameter at 1709 units is 1709 units. The beam diameter at 1710 units is 1710 units. The beam diameter at 1711 units is 1711 units. The beam diameter at 1712 units is 1712 units. The beam diameter at 1713 units is 1713 units. The beam diameter at 1714 units is 1714 units. The beam diameter at 1715 units is 1715 units. The beam diameter at 1716 units is 1716 units. The beam diameter at 1717 units is 1717 units. The beam diameter at 1718 units is 1718 units. The beam diameter at 1719 units is 1719 units. The beam diameter at 1720 units is 1720 units. The beam diameter at 1721 units is 1721 units. The beam diameter at 1722 units is 1722 units. The beam diameter at 1723 units is 1723 units. The beam diameter at 1724 units is 1724 units. The beam diameter at 1725 units is 1725 units. The beam diameter at 1726 units is 1726 units. The beam diameter at 1727 units is 1727 units. The beam diameter at 1728 units is 1728 units. The beam diameter at 1729 units is 1729 units. The beam diameter at 1730 units is 1730 units. The beam diameter at 1731 units is 1731 units. The beam diameter at 1732 units is 1732 units. The beam diameter at 1733 units is 1733 units. The beam diameter at 1734 units is 1734 units. The beam diameter at 1735 units is 1735 units. The beam diameter at 1736 units is 1736 units. The beam diameter at 1737 units is 1737 units. The beam diameter at 1738 units is 1738 units. The beam diameter at 1739 units is 1739 units. The beam diameter at 1740 units is 1740 units. The beam diameter at 1741 units is 1741 units. The beam diameter at 1742 units is 1742 units. The beam diameter at 1743 units is 1743 units. The beam diameter at 1744 units is 1744 units. The beam diameter at 1745 units is 1745 units. The beam diameter at 1746 units is 1746 units. The beam diameter at 1747 units is 1747 units. The beam diameter at 1748 units is 1748 units. The beam diameter at 1749 units is 1749 units. The beam diameter at 1750 units is 1750 units. The beam diameter at 1751 units is 1751 units. The beam diameter at 1752 units is 1752 units. The beam diameter at 1753 units is 1753 units. The beam diameter at 1754 units is 1754 units. The beam diameter at 1755 units is 1755 units. The beam diameter at 1756 units is 1756 units. The beam diameter at 1757 units is 1757 units. The beam diameter at 1758 units is 1758 units. The beam diameter at 1759 units is 1759 units. The beam diameter at 1760 units is 1760 units. The beam diameter at 1761 units is 1761 units. The beam diameter at 1762 units is 1762 units. The beam diameter at 1763 units is 1763 units. The beam diameter at 1764 units is 1764 units. The beam diameter at 1765 units is 1765 units. The beam diameter at 1766 units is 1766 units. The beam diameter at 1767 units is 1767 units. The beam diameter at 1768 units is 1768 units. The beam diameter at 1769 units is 1769 units. The beam diameter at 1770 units is 1770 units. The beam diameter at 1771 units is 1771 units. The beam diameter at 1772 units is 1772 units. The beam diameter at 1773 units is 1773 units. The beam diameter at 1774 units is 1774 units. The beam diameter at 1775 units is 1775 units. The beam diameter at 1776 units is 1776 units. The beam diameter at 1777 units is 1777 units. The beam diameter at 1778 units is 1778 units. The beam diameter at 1779 units is 1779 units. The beam diameter at 1780 units is 1780 units. The beam diameter at 1781 units is 1781 units. The beam diameter at 1782 units is 1782 units. The beam diameter at 1783 units is 1783 units. The beam diameter at 1784 units is 1784 units. The beam diameter at 1785 units is 1785 units. The beam diameter at 1786 units is 1786 units. The beam diameter at 1787 units is 1787 units. The beam diameter at 1788 units is 1788 units. The beam diameter at 1789 units is 1789 units. The beam diameter at 1790 units is 1790 units. The beam diameter at 1791 units is 1791 units. The beam diameter at 1792 units is 1792 units. The beam diameter at 1793 units is 1793 units. The beam diameter at 1794 units is 1794 units. The beam diameter at 1795 units is 1795 units. The beam diameter at 1796 units is 1796 units. The beam diameter at 1797 units is 1797 units. The beam diameter at 1798 units is 1798 units. The beam diameter at 1799 units is 1799 units. The beam diameter at 1800 units is 1800 units. The beam diameter at 1801 units is 1801 units. The beam diameter at 1802 units is 1802 units. The beam diameter at 1803 units is 1803 units. The beam diameter at 1804 units is 1804 units. The beam diameter at 1805 units is 1805 units. The beam diameter at 1806 units is 1806 units. The beam diameter at 1807 units is 1807 units. The beam diameter at 1808 units is 1808 units. The beam diameter at 1809 units is 1809 units. The beam diameter at 1810 units is 1810 units. The beam diameter at 1811 units is 1811 units. The beam diameter at 1812 units is 1812 units. The beam diameter at 1813 units is 1813 units. The beam diameter at 1814 units is 1814 units. The beam diameter at 1815 units is 1815 units. The beam diameter at 1816 units is 1816 units. The beam diameter at 1817 units is 1817 units. The beam diameter at 1818 units is 1818 units. The beam diameter at 1819 units is 1819 units. The beam diameter at 1820 units is 1820 units. The beam diameter at 1821 units is 1821 units. The beam diameter at 1822 units is 1822 units. The beam diameter at 1823 units is 1823 units. The beam diameter at 1824 units is 1824 units. The beam diameter at 1825 units is 1825 units. The beam diameter at 1826 units is 1826 units. The beam diameter at 1827 units is 1827 units. The beam diameter at 1828 units is 1828 units. The beam diameter at 1829 units is 1829 units. The beam diameter at 1830 units is 1830 units. The beam diameter at 1831 units is 1831 units. The beam diameter at 1832 units is 1832 units. The beam diameter at 1833 units is 1833 units. The beam diameter at 1834 units is 1834 units. The beam diameter at 1835 units is 1835 units. The beam diameter at 1836 units is 1836 units. The beam diameter at 1837 units is 1837 units. The beam diameter at 1838 units is 1838 units. The beam diameter at 1839 units is 1839 units. The beam diameter at 1840 units is 1840 units. The beam diameter at 1841 units is 1841 units. The beam diameter at 1842 units is 1842 units. The beam diameter at 1843 units is 1843 units. The beam diameter at 1844 units is 1844 units. The beam diameter at 1845 units is 1845 units. The beam diameter at 1846 units is 1846 units. The beam diameter at 1847 units is 1847 units. The beam diameter at 1848 units is 1848 units. The beam diameter at 1849 units is 1849 units. The beam diameter at 1850 units is 1850 units. The beam diameter at 1851 units is 1851 units. The beam diameter at 1852 units is 1852 units. The beam diameter at 1853 units is 1853 units. The beam diameter at 1854 units is 1854 units. The beam diameter at 1855 units is 1855 units. The beam diameter at 1856 units is 1856 units. The beam diameter at 1857 units is 1857 units. The beam diameter at 1858 units is 1858 units. The beam diameter at 1859 units is 1859 units. The beam diameter at 1860 units is 1860 units. The beam diameter at 1861 units is 1861 units. The beam diameter at 1862 units is 1862 units. The beam diameter at 1863 units is 1863 units. The beam diameter at 1864 units is 1864 units. The beam diameter at 1865 units is 1865 units. The beam diameter at 1866 units is 1866 units. The beam diameter at 1867 units is 1867 units. The beam diameter at 1868 units is 1868 units. The beam diameter at 1869 units is 1869 units. The beam diameter at 1870 units is 1870 units. The beam diameter at 1871 units is 1871 units. The beam diameter at 1872 units is 1872 units. The beam diameter at 1873 units is 1873 units. The beam diameter at 1874 units is 1874 units. The beam diameter at 1875 units is 1875 units. The beam diameter at 1876 units is 1876 units. The beam diameter at 1877 units is 1877 units. The beam diameter at 1878 units is 1878 units. The beam diameter at 1879 units is 1879 units. The beam diameter at 1880 units is 1880 units. The beam diameter at 1881 units is 1881 units. The beam diameter at 1882 units is 1882 units. The beam diameter at 1883 units is 1883 units. The beam diameter at 1884 units is 1884 units. The beam diameter at 1885 units is 1885 units. The beam diameter at 1886 units is 1886 units. The beam diameter at 1887 units is 1887 units. The beam diameter at 1888 units is 1888 units. The beam diameter at 1889 units is 1889 units. The beam diameter at 1890 units is 1890 units. The beam diameter at 1891 units is 1891 units. The beam diameter at 1892 units is 1892 units. The beam diameter at 1893 units is 1893 units. The beam diameter at 1894 units is 1894 units. The beam diameter at 1895 units is 1895 units. The beam diameter at 1896 units is 1896 units. The beam diameter at 1897 units is 1897 units. The beam diameter at 1898 units is 1898 units. The beam diameter at 1899 units is 1899 units. The beam diameter at 1900 units is 1900 units. The beam diameter at 1901 units is 1901 units. The beam diameter at 1902 units is 1902 units. The beam diameter at 1903 units is 1903 units. The beam diameter at 1904 units is 1904 units. The beam diameter at 1905 units is 1905 units. The beam diameter at 1906 units is 1906 units. The beam diameter at 1907 units is 1907 units. The beam diameter at 1908 units is 1908 units. The beam diameter at 1909 units is 1909 units. The beam diameter at 1910 units is 1910 units. The beam diameter at 1911 units is 1911 units. The beam diameter at 1912 units is 1912 units. The beam diameter at 1913 units is 1913 units. The beam diameter at 1914 units is 1914 units. The beam diameter at 1915 units is 1915 units. The beam diameter at 1916 units is 1916 units. The beam diameter at 1917 units is 1917 units. The beam diameter at 1918 units is 1918 units. The beam diameter at 1919 units is 1919 units. The beam diameter at 1920 units is 1920 units. The beam diameter at 1921 units is 1921 units. The beam diameter at 1922 units is 1922 units. The beam diameter at 1923 units is 1923 units. The beam diameter at 1924 units is 1924 units. The beam diameter at 1925 units is 1925 units. The beam diameter at 1926 units is 1926 units. The beam diameter at 1927 units is 1927 units. The beam diameter at 1928 units is 1928 units. The beam diameter at 1929 units is 1929 units. The beam diameter at 1930 units is 1930 units. The beam diameter at 1931 units is 1931 units. The beam diameter at 1932 units is 1932 units. The beam diameter at 1933 units is 1933 units. The beam diameter at 1934 units is 1934 units. The beam diameter at 1935 units is 1935 units. The beam diameter at 1936 units is 1936 units. The beam diameter at 1937 units is 1937 units. The beam diameter at 1938 units is 1938 units. The beam diameter at 1939 units is 1939 units. The beam diameter at 1940 units is 1940 units. The beam diameter at 1941 units is 1941 units. The beam diameter at 1942 units is 1942 units. The beam diameter at 1943 units is 1943 units. The beam diameter at 1944 units is 1944 units. The beam diameter at 1945 units is 1945 units. The beam diameter at 1946 units is 1946 units. The beam diameter at 1947 units is 1947 units. The beam diameter at 1948 units is 1948 units. The beam diameter at 1949 units is 1949 units. The beam diameter at 1950 units is 1950 units. The beam diameter at 1951 units is 1951 units. The beam diameter at 1952 units is 1952 units. The beam diameter at 1953 units is 1953 units. The beam diameter at 1954 units is 1954 units. The beam diameter at 1955 units is 1955 units. The beam diameter at 1956 units is 1956 units. The beam diameter at 1957 units is 1957 units. The beam diameter at 1958 units is 1958 units. The beam diameter at 1959 units is 1959 units. The beam diameter at 1960 units is 1960 units. The beam diameter at 1961 units is 1961 units. The beam diameter at 1962 units is 1962 units. The beam diameter at 1963 units is 1963 units. The beam diameter at 1964 units is 1964 units. The beam diameter at 1965 units is 1965 units. The beam diameter at 1966 units is 1966 units. The beam diameter at 1967 units is 1967 units. The beam diameter at 1968 units is 1968 units. The beam diameter at 1969 units is 1969 units. The beam diameter at 1970 units is 1970 units. The beam diameter at 1971 units is 1971 units. The beam diameter at 1972 units is 1972 units. The beam diameter at 1973 units is 1973 units. The beam diameter at 1974 units is 1974 units. The beam diameter at 1975 units is 1975 units. The beam diameter at 1976 units is 1976 units. The beam diameter at 1977 units is 1977 units. The beam diameter at 1978 units is 1978 units. The beam diameter at 1979 units is 1979 units. The beam diameter at 1980 units is 1980 units. The beam diameter at 1981 units is 1981 units. The beam diameter at 1982 units is 1982 units. The beam diameter at 1983 units is 1983 units. The beam diameter at 1984 units is 1984 units. The beam diameter at 1985 units is 1985 units. The beam diameter at 1986 units is 1986 units. The beam diameter at 1987 units is 1987 units. The beam diameter at 1988 units is 1988 units. The beam diameter at 1989 units is 1989 units. The beam diameter at 1990 units is 1990 units. The beam diameter at 1991 units is 1991 units. The beam diameter at 1992 units is 1992 units. The beam diameter at 1993 units is 1993 units. The beam diameter at 1994 units is 1994 units. The beam diameter at 1995 units is 1995 units. The beam diameter at 1996 units is 1996 units. The beam diameter at 1997 units is 1997 units. The beam diameter at 1998 units is 1998 units. The beam diameter at 1999 units is 1999 units. The beam diameter at 2000 units is 2000 units. The beam diameter at 2001 units is 2001 units. The beam diameter at 2002 units is 2002 units. The beam diameter at 2003 units is 2003 units. The beam diameter at 2004 units is 2004 units. The beam diameter at 2005 units is 2005 units. The beam diameter at 2006 units is 2006 units. The beam diameter at 2007 units is 2007 units. The beam diameter at 2008 units is 2008 units. The beam diameter at 2009 units is 2009 units. The beam diameter at 2010 units is 2010 units. The beam diameter at 2011 units is 2011 units. The beam diameter at 2012 units is 2012 units. The beam diameter at 2013 units is 2013 units. The beam diameter at 2014 units is 2014 units. The beam diameter at 2015 units is 2015 units. The beam diameter at 2016 units is 2016 units. The beam diameter at 2017 units is 2017 units. The beam diameter at 2018 units is 2018 units. The beam diameter at 2019 units is 2019 units. The beam diameter at 2020 units is 2020 units. The beam diameter at 2021 units is 2021 units. The beam diameter at 2022 units is 2022 units. The beam diameter at 2023 units is 2023 units. The beam diameter at 2024 units is 2024 units. The beam diameter at 2025 units is 2025 units. The beam diameter at 2026 units is 2026 units. The beam diameter at 2027 units is 2027 units. The beam diameter at 2028 units is 2028 units. The beam diameter at 2029 units is 2029 units. The beam diameter at 2030 units is 2030 units. The beam diameter at 2031 units is 2031 units. The beam diameter at 2032 units is 2032 units. The beam diameter at 2033 units is 2033 units. The beam diameter at 2034 units is 2034 units. The beam diameter at 2035 units is 2035 units. The beam diameter at 2036 units is 2036 units. The beam diameter at 2037 units is 2037 units. The beam diameter at 2038 units is 2038 units. The beam diameter at 2039 units is 2039 units. The beam diameter at 2040 units is 2040 units. The beam diameter at 2041 units is 2041 units. The beam diameter at 2042 units is 2042 units. The beam diameter at 2043 units is 2043 units. The beam diameter at 2044 units is 2044 units. The beam diameter at 2045 units is 2045 units. The beam diameter at 2046 units is 2046 units. The beam diameter at 2047 units is 2047 units. The beam diameter at 2048 units is 2048 units. The beam diameter at 2049 units is 2049 units. The beam diameter at 2050 units is 2050 units. The beam diameter at 2051 units is 2051 units. The beam diameter at 2052 units is 2052 units. The beam diameter at 2053 units is 2053 units. The beam diameter at 2054 units is 2054 units. The beam diameter at 2055 units is 2055 units. The beam diameter at 2056 units is 2056 units. The beam diameter at 2057 units is 2057 units. The beam diameter at 2058 units is 2058 units. The beam diameter at 2059 units is 2059 units. The beam diameter at 2060 units is 2060 units. The beam diameter at 2061 units is 2061 units. The beam diameter at 2062 units is 2062 units. The beam diameter at 2063 units is 2063 units. The beam diameter at 2064 units is 2064 units. The beam diameter at 2065 units is 2065 units. The beam diameter at 2066 units is 2066 units. The beam diameter at 2067 units is 2067 units. The beam diameter at 2068 units is 2068 units. The beam diameter at 2069 units is 2069 units. The beam diameter at 2070 units is 2070 units. The beam diameter at 2071 units is 2071 units. The beam diameter at 2072 units is 2072 units. The beam diameter at 2073 units is 2073 units. The beam diameter at 2074 units is 2074 units. The beam diameter at 2075 units is 2075 units. The beam diameter at 2076 units is 2076 units. The beam diameter at 2077 units is 2077 units. The beam diameter at 2078 units is 2078 units. The beam diameter at 2079 units is 2079 units. The beam diameter at 2080 units is 2080 units. The beam diameter at 2081 units is 2081 units. The beam diameter at 2082 units is 2082 units. The beam diameter at 2083 units is 2083 units. The beam diameter at 2084 units is 2084 units. The beam diameter at 2085 units is 2085 units. The beam diameter at 2086 units is 2086 units. The beam diameter at 2087 units is 2087 units. The beam diameter at 2088 units is 2088 units. The beam diameter at 2089 units is 2089 units. The beam diameter at 2090 units is 2090 units. The beam diameter at 2091 units is 2091 units. The beam diameter at 2092 units is 2092 units. The beam diameter at 2093 units is 2093 units. The beam diameter at 2094 units is 2094 units. The beam diameter at 2095 units is 2095 units. The beam diameter at 2096 units is 2096 units. The beam diameter at 2097 units is 2097 units. The beam diameter at 2098 units is 2098 units. The beam diameter at 2099 units is 2099 units. The beam diameter at 2100 units is 2100 units. The beam diameter at 2101 units is 2101 units. The beam diameter at 2102 units is 2102 units. The beam diameter at 2103 units is 2103 units. The beam diameter at 2104 units is 2104 units. The beam diameter at 2105 units is 2105 units. The beam diameter at 2106 units is 2106 units. The beam diameter at 2107 units is 2107 units. The beam diameter at 2108 units is 2108 units. The beam diameter at 2109 units is 2109 units. The beam diameter at 2110 units is 2110 units. The beam diameter at 2111 units is 2111 units. The beam diameter at 2112 units is 2112 units. The beam diameter at 2113 units is 2113 units. The beam diameter at 2114 units is 2114 units. The beam diameter at 2115 units is 2115 units. The beam diameter at 2116 units is 2116 units. The beam diameter at 2117 units is 2117 units. The beam diameter at 2118 units is 2118 units. The beam diameter at 2119 units is 2119 units. The beam diameter at 2120 units is 2120 units. The beam diameter at 2121 units is 2121 units. The beam diameter at 2122 units is 2122 units. The beam diameter at 2123 units is 2123 units. The beam diameter at 2124 units is 2124 units. The beam diameter at 2125 units is 2125 units. The beam diameter at 2126 units is 2126 units. The beam diameter at 2127 units is 2127 units. The beam diameter at 2128 units is 2128 units. The beam diameter at 2129 units is 2129 units. The beam diameter at 2130 units is 2130 units. The beam diameter at 2131 units is 2131 units. The beam diameter at 2132 units is 2132 units. The beam diameter at 2133 units is 2133 units. The beam diameter at 2134 units is 2134 units. The beam diameter at 2135 units is 2135 units. The beam diameter at 2136 units is 2136 units. The beam diameter at 2137 units is 2137 units. The beam diameter at 2138 units is 2138 units. The beam diameter at 2139 units is 2139 units. The beam diameter at 2140 units is 2140 units. The beam diameter at 2141 units is 2141 units. The beam diameter at 2142 units is 2142 units. The beam diameter at 2143 units is 2143 units. The beam diameter at 2144 units is 2144 units. The beam diameter at 2145 units is 2145 units. The beam diameter at 2146 units is 2146 units. The beam diameter at 2147 units is 2147 units. The beam diameter at 2148 units is 2148 units. The beam diameter at 2149 units is 2149 units. The beam diameter at 2150 units is 2150 units. The beam diameter at 2151 units is 2151 units. The beam diameter at 2152 units is 2152 units. The beam diameter at 2153 units is 2153 units. The beam diameter at 2154 units is 2154 units. The beam diameter at 2155 units is 2155 units. The beam diameter at 2156 units is 2156 units. The beam diameter at 2157 units is 2157 units. The beam diameter at 2158 units is 2158 units. The beam diameter at 2159 units is 2159 units. The beam diameter at 2160 units is 2160 units. The beam diameter at 2161 units is 2161 units. The beam diameter at 2162 units is 2162 units. The beam diameter at 2163 units is 2163 units. The beam diameter at 2164 units is 2164 units. The beam diameter at 2165 units is 2165 units. The beam diameter at 2166 units is 2166 units. The beam diameter at 2167 units is 2167 units. The beam diameter at 2168 units is 2168 units. The beam diameter at 2169 units is 2169 units. The beam diameter at 2170 units is 2170 units. The beam diameter at 2171 units is 2171 units. The beam diameter at 2172 units is 2172 units. The beam diameter at 2173 units is 2173 units. The beam diameter at 2174 units is 2174 units. The beam diameter at 2175 units is 2175 units. The beam diameter at 2176 units is 2176 units. The beam diameter at 2177 units is 2177 units. The beam diameter at 2178 units is 2178 units. The beam diameter at 2179 units is 2179 units. The beam diameter at 2180 units is 2180 units. The beam diameter at 2181 units is 2181 units. The beam diameter at 2182 units is 2182 units. The beam diameter at 2183 units is 2183 units. The beam diameter at 2184 units is 2184 units. The beam diameter at 2185 units is 2185 units. The beam diameter at 2186 units is 2186 units. The beam diameter at 2187 units is 2187 units. The beam diameter at 2188 units is 2188 units. The beam diameter at 2189 units is 2189 units. The beam diameter at 2190 units is 2190 units. The beam diameter at 2191 units is 2191 units. The beam diameter at 2192 units is 2192 units. The beam diameter at 2193 units is 2193 units. The beam diameter at 2194 units is 2194 units. The beam diameter at 2195 units is 2195 units. The beam diameter at 2196 units is 2196 units. The beam diameter at 2197 units is 2197 units. The beam diameter at 2198 units is 2198 units. The beam diameter at 2199 units is 2199 units. The beam diameter at 2200 units is 2200 units. The beam diameter at 2201 units is 2201 units. The beam diameter at 2202 units is 2202 units. The beam diameter at 2203 units is 2203 units. The beam diameter at 2204 units is 2204 units. The beam diameter at 2205 units is 2205 units. The beam diameter at 2206 units is 2206 units. The beam diameter at 2207 units is 2207 units. The beam diameter at 2208 units is 2208 units. The beam diameter at 2209 units is 2209 units. The beam diameter at 2210 units is 2210 units. The beam diameter at 2211 units is 2211 units. The beam diameter at 2212 units is 2212 units. The beam diameter at 2213 units is 2213 units. The beam diameter at 2214 units is 2214 units. The beam diameter at 2215 units is 2215 units. The beam diameter at 2216 units is 2216 units. The beam diameter at 2217 units is 2217 units. The beam diameter at 2218 units is 2218 units. The beam diameter at 2219 units is 2219 units. The beam diameter at 2220 units is 2220 units. The beam diameter at 2221 units is 2221 units. The beam diameter at 2222 units is 2222 units. The beam diameter at 2223 units is 2223 units. The beam diameter at 2224 units is 2224 units. The beam diameter at 2225 units is 2225 units. The beam diameter at 2226 units is 2226 units. The beam diameter at 2227 units is 2227 units. The beam diameter at 2228 units is 2228 units. The beam diameter at 2229 units is 2229 units. The beam diameter at 2230 units is 2230 units. The beam diameter at 2231 units is 2231 units. The beam diameter at 2232 units is 2232 units. The beam diameter at 2233 units is 2233 units. The beam diameter at 2234 units is 2234 units. The beam diameter at 2235 units is 2235 units. The beam diameter at 2236 units is 2236 units. The beam diameter at 2237 units is 2237 units. The beam diameter at 2238 units is 2238 units. The beam diameter at 2239 units is 2239 units. The beam diameter at 2240 units is 2240 units. The beam diameter at 2241 units is 2241 units. The beam diameter at 2242 units is 2242 units. The beam diameter at 2243 units is 2243 units. The beam diameter at 2244 units is 2244 units. The beam diameter at 2245 units is 2245 units. The beam diameter at 2246 units is 2246 units. The beam diameter at 2247 units is 2247 units. The beam diameter at 2248 units is 2248 units. The beam diameter at 2249 units is 2249 units. The beam diameter at 2250 units is 2250 units. The beam diameter at 2251 units is 2251 units. The beam diameter at 2252 units is 2252 units. The beam diameter at 2253 units is 2253 units. The beam diameter at 2254 units is 2254 units. The beam diameter at 2255 units is 2255 units. The beam diameter at 2256 units is 2256 units. The beam diameter at 2257 units is 2257 units. The beam diameter at 2258 units is 2258 units. The beam diameter at 2259 units is 2259 units. The beam diameter at 2260 units is 2260 units. The beam diameter at 2261 units is 2261 units. The beam diameter at 2262 units is 2262 units. The beam diameter at 2263 units is 2263 units. The beam diameter at 2264 units is 2264 units. The beam diameter at 2265 units is 2265 units. The beam diameter at 2266 units is 2266 units. The beam diameter at 2267 units is 2267 units. The beam diameter at 2268 units is 2268 units. The beam diameter at 2269 units is 2269 units. The beam diameter at 2270 units is 2270 units. The beam diameter at 2271 units is 2271 units. The beam diameter at 2272 units is 2272 units. The beam diameter at 2273 units is 2273 units. The beam diameter at 2274 units is 2274 units. The beam diameter at 2275 units is 2275 units. The beam diameter at 2276 units is 2276 units. The beam diameter at 2277 units is 2277 units. The beam diameter at 2278 units is 2278 units. The beam diameter at 2279 units is 2279 units. The beam diameter at 2280 units is 2280 units. The beam diameter at 2281 units is 2281 units. The beam diameter at 2282 units is 2282 units. The beam diameter at 2283 units is 2283 units. The beam diameter at 2284 units is 2284 units. The beam diameter at 2285 units is 2285 units.

Technische
Daten

Konzept

LED-Einbau-Stableuchte.

Lichtquelle

LED-Streifenplatten Low Power High Efficiency Ra80. 2700K-3500K auf Anfrage.

Die Energieeffizienzklasse des Produkts	D
Nennleistung	24W
Nenn-Lichtstrom	3420lm
Farbwiedergabeindex	80
R _f	82,9
R _g	97
Ähnliche Farbtemperatur	3000K
SDCM	2
Lebensdauer (L80/B10)	100000h tq +25°C
Lebensdauer (L90/B10)	59000h tq +25°C

TARGETTI

CCIAA Firenze
Share Capital: € 500.000,00
USt.-ID. (IT): 01537660480
Handelsregistereintrag: FI-275656

Targetti Sankey S.r.l.
Via Giuseppe Garibaldi, 82
50041 Calenzano (FI)
Italy

Tel: +39 055 37911
targetti.com
targetti@targetti.com

Aus Gründen der technologischen Entwicklung der elektronischen Bauteile unterliegen die aufgeführten Daten eventuellen Aktualisierungen. Daher muss bei der Bestellung eine Bestätigung angefordert werden.
Der Lichtstrom und die elektrische Leistung weisen einen Toleranzbereich von +/-10% im Vergleich zum angezeigten Wert auf. Tq bei +25 °C auf (CIE 121).

Technische Änderungen vorbehalten.

Technische Daten

Beleuchtungstechnische Merkmale

Interne Optikgruppe bestehend aus zylindrischer Primärlinse aus Glas, Reflektor aus hochreflektierendem eloxiertem Aluminium und integriertem holographischem Filter.

Optik	Grazing
Abstrahlwinkel	GRZ
Optische Effizienz	86,58%
Leuchten-Lichtstrom	2961lm
Lichtausbeute	106lm/W
Fotobiologische Sicherheit	Risikogruppe 1 (RG 1 = geringes Risiko)

Mechanische Merkmale

Gehäuse aus eloxiertem extrudiertem Aluminium 15µ. Flache Abdeckung aus 10 mm dickem extra klarem Glas. Rahmen aus gebürstetem Edelstahl (AISI 316). Das Leuchtengehäuse ist gegen eine statische Last von bis zu 20 kN beständig und vandalismussicher (IK10). Rutschhemmendes Glas ist auf Anfrage erhältlich.

Farbe und Oberfläche	Aluminium
Abmessungen	AxBxH 616x91x88mm
Gewicht	3,8Kg
Schutzart	IP66,IP67,IP68,IP69
Mechanische Belastbarkeit	IK10

Elektrische Merkmale

Integriertes elektronisches Betriebsgerät. Einschließlich Verbindungsstecker mit Schutzart IP68 für die Stromversorgung. Zu ergänzen mit dem Set wasserdichter IP68-Verbindungsstecker (IN-OUT) mit Schnellmontagesystem (1E2769) oder mit Anschlusskabel inklusive 5-poliger Verbindungsstecker (1E2762, 1E2763, 1E2764, 1E2765). Leuchte mit integrierter Durchgangsverdrahtung. Leuchten gemäß EN 60598-2-22 für die Stromversorgung über ein zentrales Notstromsystem CPSS (Central Power Supply System); Bereiche mit hohem Risiko ausgeschlossen. Die voreingestellte Leistungsaufnahme und der voreingestellte Lichtstrom betragen 100% an AC und 100% an DC.

Leistungsaufnahme der Leuchte	28W
Betriebsgerät	220-240Vac 50/60Hz
Schutzklasse	SCHUTZKLASSE 1
Treiberart / Steuerung	ON-OFF
einschließlich Treiber	JA
SAFE FLICKER	PstLM=<1 und SVM=<0,4 (IEC TR 61547-1 und IEC TR 63158), um ein angenehmeres und sicheres Licht zu garantieren
Umgebungstemperaturen	-25°C / +40°C

Installation

Zu ergänzen mit entsprechendem Einbaugehäuse aus eloxiertem Aluminium für den Anschluss in Reihe.

Hinweise

Das Produkt ist mit der technischen Lösung "Waterblock Smart" ausgestattet, bei der die Anschlusskabel mit Harz beschichtet werden, wodurch die Gefahr, dass Feuchtigkeit zum Treiber oder zur Leuchte aufsteigt, gemindert wird. Die 110-277Vac Version ist auf Anfrage erhältlich. IP68: der Strahler darf nicht dauerhaft unter Wasser installiert werden, kann aber versehentlich kurzzeitig bis zu einer Tiefe von 2 m (max.24h) untergetaucht sein. IP69: IEC/EN 60529 Normkonform.

TARGETTI

CCIAA Firenze
Share Capital: € 500.000,00
USt.-ID. (IT): 01537660480
Handelsregistereintrag: FI-275656

Targetti Sankey S.r.l.
Via Giuseppe Garibaldi, 82
50041 Calenzano (FI)
Italy

Tel: +39 055 37911
targetti.com
targetti@targetti.com

Aus Gründen der technologischen Entwicklung der elektronischen Bauteile unterliegen die aufgeführten Daten eventuellen Aktualisierungen. Daher muss bei der Bestellung eine Bestätigung angefordert werden. Der Lichtstrom und die elektrische Leistung weisen einen Toleranzbereich von +/-10% im Vergleich zum angezeigten Wert auf. Tq bei +25 °C auf (CIE 121).

Technische Änderungen vorbehalten.

Technische Daten

Garantie

5 Jahre.

Hinweise

Leuchte für die Entsorgung/Recycling am Ende der Lebensdauer konzipiert. Austauschbare (nur LED) Lichtquelle durch einen Fachmann. Austauschbare Vorschaltgeräte durch einen Fachmann.

TARGETTI

CCIAA Firenze
Share Capital: € 500.000,00
USt.-ID. (IT): 01537660480
Handelsregistereintrag: FI-275656

Targetti Sankey S.r.l.
Via Giuseppe Garibaldi, 82
50041 Calenzano (FI)
Italy

Tel: +39 055 37911
targetti.com
targetti@targetti.com

Aus Gründen der technologischen Entwicklung der elektronischen Bauteile unterliegen die aufgeführten Daten eventuellen Aktualisierungen. Daher muss bei der Bestellung eine Bestätigung angefordert werden. Der Lichtstrom und die elektrische Leistung weisen einen Toleranzbereich von +/-10% im Vergleich zum angezeigten Wert auf. Tq bei +25 °C auf (CIE 121).

Technische Änderungen vorbehalten.

Artikelnummern für notwendiges Zubehör

Einbaugehäuse



ART.-NR.	L
1E3507	618mm

Einbaugehäuse aus anodisiertem extrudiertem Aluminium.

Zubehör

Werkzeug




ART.-NR.

1E2495

Schlüssel TORX L-KEY. Mit Kopf TORX TX 30.

Kabel



ART.-NR.	L
1E2762	320mm
1E2763	470mm
1E2764	620mm
1E2765	770mm

Verbindungsleitung.
Einschließlich 5-poliger Verbindungsstecker.
Für die ON-OFF Version oder DALI.

1E2762 - Zum aneinandergrenzenden Anschluss in Reihe eines 600-mm-Strahlers und eines 900-mm-Strahlers.

1E2763 - Zum aneinandergrenzenden Anschluss in Reihe eines 600-mm-Strahlers und eines 1200-mm-Strahlers oder zweier 900-mm-Strahler.

1E2764 - Zum aneinandergrenzenden Anschluss in Reihe eines 900-mm-Strahlers und eines 1200-mm-Strahlers.

1E2765 - Zum aneinandergrenzenden Anschluss in Reihe zweier 1200-mm-Strahler.

Verbinder




ART.-NR.

1E2769

Lineare Anschlussbox IP66/IP68.
5-polig, Leitungsdurchmesser max. 1,5mm².
Kabeldurchmesser von 7 bis 12mm.

Überspannungsschutz



ART.-NR.

A013A

Überspannungsschutz kompatibel mit Beleuchtungskörpern der SCHUTZKLASSE I.
Betriebsspannung 230—277Vac.
SPD Typ 2+3.
Maximale Entladespannung 10kV.
SCHUTZKLASSE I
IP67



CCIAA Firenze
Share Capital: € 500.000,00
USt.-ID. (IT): 01537660480
Handelsregistereintrag: FI-275656

Targetti Sankey S.r.l.
Via Giuseppe Garibaldi, 82
50041 Calenzano (FI)
Italy

Tel: +39 055 37911
targetti.com
targetti@targetti.com

Aus Gründen der technologischen Entwicklung der elektronischen Bauteile unterliegen die aufgeführten Daten eventuellen Aktualisierungen. Daher muss bei der Bestellung eine Bestätigung angefordert werden. Der Lichtstrom und die elektrische Leistung weisen einen Toleranzbereich von +/-10% im Vergleich zum angezeigten Wert auf. Tq bei +25 °C auf (CIE 121).

Technische Änderungen vorbehalten.